



15NBX100

LF Drivers - 15.0 Inches









- 2000 W continuous program power capacity
- 100 mm (4 in) copper voice coil
- 35 1500 Hz response
- 97 dB sensitivity
- FEA optimized Neodymium magnet assembly
- Aluminium demodulating ring allows a very low distortion figure
- Double silicone spider with optimized compliance
- Ventilated voice coil gap for reduced power compression



LF Drivers- 15.0 Inches





SPECIFICATIONS

Nominal Diameter	380 mm (15.0 in)
Nominal Impedance	8 Ω
Minimum Impedance	6.4 Ω
Nominal Power Handling ¹	1000 W
Continuous Power Handling ²	2000 W
Sensitivity ³	97.0 dB
Frequency Range	35 - 1500 Hz
Voice Coil Diameter	100 mm (4.0 in)
Winding Material	Copper
Former Material	Glass Fibre
Winding Depth	25.0 mm (1.0 in)
Magnetic Gap Depth	11.0 mm (0.43 in)
Flux Density	1.1 T

DESIGN

Surround Shape	Triple Roll
Cone Shape	Exponential
Magnet Material	Neodymium Inside Slug
Spider	Double Silicone
Pole Design	T-Pole
Woofer Cone Treatment	t P Waterproof Both Sides
Recommended Enclosur	re 114.0 dm 3 (4.0 ft 3)
Recommended Tuning	35 Hz

PARAMETERS⁴

Resonance Frequency	36 Hz
Re	5.1 Ω
Qes	0.31
Qms	4.2
Qts	0.29
Vas	125.0 dm ³ (4.4 ft ³)
Sd	855.0 cm ² (132.5 in ²)
ηο	2.0 %
Xmax	10.0 mm
Xvar	10.0 mm
Mms	151.0 g
Bl	25.0 Txm
Le	2.0 mH
EBP	116 Hz

MOUNTING AND SHIPPING INFO

Overall Diameter	393 mm (15.5 in)
Bolt Circle Diameter	374 mm (16.7 in)
Baffle Cutout Diameter	353.0 mm (13.9 in)
Depth	179 mm (7.05 in)
Flange and Gasket Thickne	ess 14 mm (0.55 in)
Air Volume Occupied by Dr	river
7 iii voluitie occupica by bi	1001
741 Volume occupied by Di	6.0 dm ³ (0.21 ft ³)
Net Weight	
	6.0 dm ³ (0.21 ft ³)
Net Weight	6.0 dm ³ (0.21 ft ³) 9.0 kg (19.8 lb)

SERVICE KIT

RCK15NBX1008

- 2 hours test made with continuous pink noise signal within the range Fs-10Fs. Power calculated on rated nominal impedance. Loudspeaker in free air.
 Power on Continuous Program is defined as 3 dB greater than the Nominal rating.
 Applied RMS Voltage is set to 2.83 V for 8 ohms Nominal Impedance.
 Thiele-Small parameters are measured after a high level 20 Hz sine wave preconditioning test.